

Reveria Press PC1120 Functions & Specifications

Basic Specifications / Print Function

Item		Description
Colour Capability		Full Colour
Printing Resolution		2400 x 2400 dpi
Continuous Print Speed^{*1}	A4	120 ppm
	A3	60 ppm
Paper Size^{*2 *3}		Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A6 Custom Size: 98 x 148 mm to 330 x 488 mm ^{*4}
Paper Weight		52 to 400 gsm ^{*5}
Paper Tray Capacity^{*6}	Standard	2000 sheets x 2-tray
	Optional	[Multi Sheet Inserter / Multi Sheet Inserter for Banner Print ^{*7}] 250 sheets [High Capacity Feeder C3-DS] 2000 sheets x 2-tray [2nd High Capacity Feeder C1-DS] 2000 sheets x 2-tray [Air Suction Feeder C1-DS] 2100 sheets x 2-tray + 250 sheets [Air Suction Feeder C1-DSXL + Banner Unit for Air Suction Feeder C1-DSXL] 800 sheets + 2100 sheets + 250 sheets [Chained Air Suction Feeder C1-DS-R + Chained Air Suction Feeder C1-DS-L] 2100 sheets x 2-tray x 2-connection + 250 sheets [Chained Air Suction Feeder C1-DS-R + Chained Air Suction Feeder C1-DSXL-L + Banner Unit for Air Suction Feeder C1-DSXL] 2100 sheets x 2-tray + 800 sheets + 2100 sheets + 250 sheets
	Max	12650 sheets [Standard + Chained Air Suction Feeder C1-DS-R + Chained Air Suction Feeder C1-DS-L]
Output Tray Capacity^{*6 *8}		500 sheets
Power Supply		AC200-240 V +/- 10 %, 44 A, 50/60 Hz common
Maximum Power Consumption		9.0 kW
Dimensions^{*9}		W 2995 x D 1104 x H 1786 mm
Weight^{*9}		1558 kg

*1: When continuously printing a single sided document. 52 to 400 gsm, uncoated paper. Print speed may be reduced depending on conditions of output data, on whether auto image quality adjustment is performed, on whether the job includes a mixture of paper sizes and types, and other reasons.

*2: Image loss width: Lead edge 4.0 mm, Trail edge 2.0 mm, Front 2.0 mm, Rear 2.0 mm.

*3: When setting main scanning 98 to 182 mm paper, Post Card Kit 2 is required.

*4: Banner sheet printing of up to 330 x 1200 mm is available (Optional).

*5: Banner sheet printing of 82 to 300 gsm is available (Optional).

*6: 90 gsm paper.

*7: Multi Sheet Inserter and Multi Sheet Inserter for Banner Print are options for High Capacity Feeder C3-DS.

*8: Offset Catch Tray.

*9: Main unit only. Excludes output tray.

Print Server [Revoria Flow PC21]

Item	Description
Type	External
CPU	Intel® Xeon® E-2388G Processor (3.20 GHz)
Storage device	SSD: 3.84 TB (System) + 3.84 TB x 2 (Spool), DVD Multi drive
Memory capacity	64 GB (Max: 64 GB)
Server Operation System	Windows 10 IoT Enterprise LTSC 2021 (64bit)
Page Description Language	Adobe® PostScript® 3™, PDF/VT-1, PDF/VT-2, PPML, VIPP ^{*1}
Print Data Format	PS, PDF2.0, PDF/X-1a, PDF/X-3, PDF/X-4, PDF/X-5, EPS, TIFF, JPEG
Supported Operating System ^{*2}	Windows 11 (64 bit), Windows 10 (32bit / 64bit), Windows Server 2022 (64bit), Windows Server 2019 (64bit), Windows Server 2016 (64bit), Windows Server 2012 R2 (64bit), Windows Server 2012 (64bit) macOS 13 / 12 / 11 / 10.15 / 10.14 / 10.13
Interface	Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T x 2 USB3.2 Type C x 1 (front side), USB3.2 x 3 (front side x 1, back side x 2), USB2.0 x 4 (back side)
Network Protocol	TCP/IP (lpd / FTP / IPP ^{*3} / SMB / JDF / HTTP), Bonjour
Power Supply	AC100-240 V +/- 10 %, 6.0 A (100V) / 2.9 A (240 V), 50/60 Hz common
Maximum Power Consumption	0.5 kW
Dimensions ^{*4*5}	W 178 x D 522x H 457 mm
Weight ^{*4}	19 kg

*1: Used with optional software Xerox FreeFlow VI Compose.

*2: Please refer to our official website for the latest supported OS.

*3: Used to work with Xerox FreeFlow Digital Workflow Collection.

*4: Print Server only. Excludes Monitor, mouse and keyboard.

*5: Depth is 547 mm including protrusions.

High Capacity Feeder C3-DS (Optional)

Item	Description
Paper Size	High Capacity Feeder^{*1} Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A6 Custom Size: 98 x 148 mm to 330 x 488 mm
	Bypass Tray^{*2} Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A6 Custom Size: 98 x 148 mm to 330 x 488 mm ^{*3}
Paper Weight	High Capacity Feeder 52 to 350 gsm
	Bypass Tray^{*2} 52 to 300 gsm ^{*4}
Feeding Capacity / Number of Tray ^{*5}	High Capacity Feeder 2000 sheets x 2-tray
	Bypass Tray^{*2} 250 sheets
Power Supply	AC100-120 V +/- 10 %, 6 A, AC220-240 V +/- 10 %, 4 A, 50/60 Hz common
Maximum Power Consumption	880 W
Dimensions	W 988 x D 762 x H 992 mm
Weight ^{*6}	215 kg

Note: Optional Multi Sheet Inserter or Multi Sheet Inserter for Banner Print is required.

*1: When setting main scanning 98 to 182 mm paper, Post Card Kit 2 is required.

*2: Multi Sheet Inserter or Multi Sheet Inserter for Banner Print (Optional).

*3: Banner sheet printing of up to 330 x 1200 mm is available (Optional).

*4: Banner sheet printing of 82 to 300 gsm is available (Optional).

*5: 90 gsm paper.

*6: Including the optional Multi Sheet Inserter or Multi Sheet Inserter for Banner Print.

2nd High Capacity Feeder C1-DS (Optional)

Item		Description
Paper Size	High Capacity Feeder ^{*1}	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A6 Custom Size: 98 x 148 mm to 330 x 488 mm
Paper Weight	High Capacity Feeder	52 to 350 gsm
Feeding Capacity / Number of Tray ^{*2}	High Capacity Feeder	2000 sheets x 2-tray
Power Supply		AC100-120 V +/- 10 %, 6 A, AC220-240 V +/- 10 %, 4 A, 50/60 Hz common
Maximum Power Consumption		880 W
Dimensions		W 988 x D 762 x H 992 mm
Weight		235 kg

*1: When setting main scanning 98 to 182 mm paper, Post Card Kit 2 is required.

*2: 90 gsm paper.

Air Suction Feeder C1-DS / C1-DSXL (Optional)

Item	Description	
	Air Suction Feeder C1-DS	Air Suction Feeder C1-DSXL + Banner Unit for Air Suction Feeder C1-DSXL
Paper Size ^{*1}	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A6 Custom Size: 98 x 148 mm to 330 x 488 mm	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A6 Custom Size: 210 x 210 mm to 330 x 1200 mm ^{*2} (Upper tray), 98 x 148 mm to 330 x 488 mm (Lower tray)
Paper Weight	52 to 400 gsm ^{*3}	
Feeding Capacity / Number of Tray ^{*4}	2100 sheets x 2-tray + 250 sheets	800 sheets ^{*5} + 2100 sheets + 250 sheets
Power Supply	AC100-120 V +/- 10 %, 5 A, AC220-240 V +/- 10 %, 4 A, 50/60 Hz common	
Maximum Power Consumption	880 W	
Dimensions	W 988 x D 762 x H 992 mm	W 1580 x D 762 x H 992 mm
Weight ^{*6}	194 kg	213 kg

Note: Multi Sheet Inserter for Banner Print is included.

Note: Air Suction Feeder C1-DSXL and Banner Unit for Air Suction Feeder C1-DSXL are required as a set.

Note: Air Suction Feeder C1-DSXL can feed long paper only from the Upper tray.

*1: When setting main scanning 98 to 182 mm paper, Post Card Kit for Air Suction Feeder is required.

*2: Duplex Automatic Print supports paper size up to 330 x 729 mm.

*3: For long paper from 330 x 488 mm to 330 x 660 mm: 52 to 350 gsm; for paper up to 330 x 729 mm: 52 to 300 gsm; for paper up to 330 x 1200 mm: 52 to 256 gsm. Duplex Automatic Print supports paper weight up to 300 gsm.

*4: 90 gsm paper.

*5: 100 sheets for paper longer than 729 mm (90 gsm).

*6: Including Multi Sheet Inserter for Banner Print.

Chained Air Suction Feeder C1-DS / C1-DSXL (Optional)

Item	Description	
	Chained Air Suction Feeder C1-DS-R + Chained Air Suction Feeder C1-DS-L	Chained Air Suction Feeder C1-DS-R + Chained Air Suction Feeder C1-DSXL-L + Banner Unit for Air Suction Feeder C1-DSXL
Paper Size ^{*1}	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A6 Custom Size: 98 x 148 mm to 330 x 488 mm	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A6 Custom Size: 98 x 148 mm to 330 x 488 mm, 210 x 210 mm to 330 x 1200 mm ^{*2} (Upper tray of the left module)
Paper Weight	52 to 400 gsm ^{*3}	
Feeding Capacity / Number of Tray ^{*4}	2100 sheets x 2-tray x 2-connection + 250 sheets	2100 sheets x 2-tray + 800 sheets ^{*5} + 2100 sheets + 250 sheets
Power Supply	AC100-120 V +/- 10 %, 5 A, AC220-240 V +/- 10 %, 4 A, 50/60 Hz common x 2 Power	
Maximum Power Consumption	880 W x 2 Power	
Dimensions	W 1980 x D 762 x H 992 mm	W 2572 x D 762 x H 992 mm
Weight ^{*6}	403 kg	420 kg

Note: Multi Sheet Inserter for Banner Print is included.

Note: Chained Air Suction Feeder C1-DS-R and C1-DS-L are required as a set.

Note: Chained Air Suction Feeder C1-DS-R, C1-DSXL-L and Banner Unit for Air Suction Feeder C1-DSXL are required as a set.

Note: Chained Air Suction Feeder C1-DSXL-L can feed long paper only from the Upper tray.

*1: When setting main scanning 98 to 182 mm paper, Post Card Kit for Air Suction Feeder is required.

*2: Duplex Automatic Print supports paper size up to 330 x 729 mm.

*3: For long paper from 330 x 488 mm to 330 x 660 mm: 52 to 350 gsm; for paper up to 330 x 729 mm: 52 to 300 gsm; for paper up to 330 x 1200 mm: 52 to 256 gsm. Duplex Automatic Print supports paper weight up to 300 gsm.

*4: 90 gsm paper.

*5: 100 sheets for paper longer than 729 mm (90 gsm).

*6: Including Multi Sheet Inserter for Banner Print.

Catch Tray (Optional)

Item	Description	
	Offset Catch Tray	Long Catch Tray
Paper Size	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A6 ^{*1} Custom Size: 98 x 148 mm to 330 x 488 mm ^{*1}	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A6 Custom Size: 98 x 148 mm to 330 x 1200 mm
Paper Weight	52 to 400 gsm ^{*2}	52 to 400 gsm ^{*3}
Paper Capacity ^{*4}	500 sheets	300 sheets (Paper length up to 488 mm) 100 sheets (Paper length above 489 to 729 mm) 10 sheets (Paper length above 730 to 1200 mm)
Dimensions	W 406 x D 393 x H 184 mm	W 512 x D 396 x H 308 mm ^{*5}
Weight	6 kg	4 kg ^{*6}

Note: Offset Catch Tray Enabling Kit is required.

*1: With an offset, standard size is A3 at a maximum and JIS B5 at a minimum. Custom size is from 171 x 182 mm to 297 x 488 mm.

*2: With an offset, it is 300 gsm at a maximum.

*3: Banner sheet printing of 82 to 300 gsm is available (Optional).

*4: 90 gsm paper.

*5: When Long Paper Extension Kit is installed, W 941 x D 396 x H 495 mm.

*6: When Long Paper Extension Kit is installed, 5 kg.

Finisher D6 / Finisher D6 with Booklet Maker (Optional)

Item		Description	
		Finisher D6	Finisher D6 with Booklet Maker
Type	Output Tray	Sort / Stack	
	Finishing Tray	Sort (Offset available) / Stack (Offset available)	
	Booklet Tray	-	Sort / Stack
Paper Size	Output Tray	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A6 Custom Size: 98 x 148 mm to 330 x 1200 mm ^{*1}	
	Finishing Tray	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A5 Custom Size: 148 x 148 mm to 330 x 488 mm	
Paper Weight	Output Tray	52 to 400 gsm	
	Finishing Tray	52 to 350 gsm	
Paper Capacity ^{*2}	Output Tray	500 sheets (A4)	
	Finishing Tray	[Without Stapling] A4: 3000 sheets JIS B4 or larger: 1500 sheets Mixed Size Stacking ^{*3} : 350 sheets [With Stapling] A4: 200 sets or 3000 sheets JIS B4 or larger: 100 sets or 1500 sheets	[Without Stapling] A4: 2000 sheets JIS B4 or larger: 1500 sheets Mixed Size Stacking ^{*3} : 350 sheets [With Stapling] A4: 200 sets or 2000 sheets JIS B4 or larger: 100 sets or 1500 sheets
	Booklet Tray	-	20 sets ^{*4}
Staple	Capacity	100 sheets (90 gsm or less) ^{*5}	
	Paper Size ^{*6}	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min JIS B5 Custom Size: 182 x 182 mm to 297 x 432 mm	
	Paper Weight	52 to 350 gsm	
	Position	Single stapling, Dual stapling, 4 stapling	
Punch ^{*7}	Number of Holes	2-hole / 4-hole punch or 2-hole / 3-hole punch (US Specifications)	
	Paper Size ^{*8}	Standard Size: Max A3, 11 x 17", Min JIS B5 (2-hole punch, 3-hole punch), A4 (4-hole punch) Custom Size: 203 x 182 mm to 297 x 431 mm	
	Paper Weight	52 to 220 gsm	
Booklet Finishing	Capacity ^{*9}	-	Saddle Staple: 30 sheets (90 gsm or less) Single Fold: 5 sheets (220 gsm or less)
	Paper Size	-	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min JIS B5 Custom Size: 182 x 257 mm to 330 x 488 mm
	Paper Weight	-	60 to 350 gsm
Power Supply	AC100-127 V +/- 10 %, 3 A, AC200-240 V +/- 10 %, 1.5 A, 50/60 Hz common		
Maximum Power Consumption	360 W		
Dimensions	W 855 x D 725 x H 1204 mm When Folder Unit CD2 is installed: W 1092 x D 725 x H 1204 mm	W 892 x D 725 x H 1204 mm When Folder Unit CD2 is installed: W 1129 x D 725 x H 1204 mm	
Weight	87 kg When Folder Unit CD2 is installed: 142 kg	107 kg When Folder Unit CD2 is installed: 162 kg	

Note: Interface Decurler Module D1 is required.

*1: For paper longer than 330 x 488 mm, the capacity is not guaranteed. When the optional Banner Print Extension Kit is installed, 150 sheets of long paper up to 330 x 660 mm; 100 sheets of long paper up to 330 x 729 mm; 10 sheets of long paper up to 330 x 1200 mm can be stacked.

*2: 90 gsm paper.

*3: When larger size sheets are stacked on top of smaller size sheets.

*4: 16 sets when 17-20 sheets/set, 12 sets when 21-25 sheets/set, 10 sets when 26-30 sheets/set.

*5: 65 sheets for sizes exceeding A4.

*6: Available staple positions vary depending on the paper size.

*7: Optional.

*8: Available number of punch holes varies depending on the paper size.

*9: The maximum number of sheets varies depending on the paper weight. Booklet may not be tightly closed depending on the size or type of the paper.

Folder Unit CD2 (Optional)

Item		Description
Z Fold Half Sheet	Paper Size	A3, 11 x 17", JIS B4
	Paper Weight	60 to 90 gsm
Tri-fold	Paper Size	A4, Letter
	Paper Weight	60 to 90 gsm
	Paper Capacity*	30 sheets
Power Supply		AC100-127 V +/- 10 %, 1 A, AC200-240 V +/- 10 %, 0.5 A, 50/60 Hz common
Maximum Power Consumption		120 W
Dimensions		W 232 x D 725 x H 992 mm
Weight		55 kg

Note: Folder Unit CD2 is option for Finisher D6 and Finisher D6 with Booklet Maker.

*: 80 gsm paper.

High Capacity Stacker A1 / High Capacity Stacker A1 with Transport Module (Optional)

Item		Description	
		High Capacity Stacker A1	High Capacity Stacker A1 with Transport Module
Paper Capacity*1	Output Tray	500 sheets*2	
	High Capacity Stacker - Stacker Cart	5000 sheets	
Paper Size	Output Tray	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A6 Custom Size: 98 x 148 mm to 330 x 488 mm*3	
	High Capacity Stacker - Stacker Cart	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min JIS B5 Custom Size: 203 x 182 mm to 330 x 488 mm	
Paper Weight	Output Tray	52 to 400 gsm	
	High Capacity Stacker - Stacker Cart	52 to 300 gsm	
Power Supply		AC100-240 V +/- 10 %, 1.5 A (100 V) / 0.8 A (240 V), 50/60 Hz common	
Maximum Power Consumption		192 W	
Dimensions		W 800 x D 725 x H 1042 mm	W 848 x D 725 x H 1042 mm
Weight*4		155 kg	159 kg

Note: Interface Decurler Module D1 is required.

Note: High Capacity Stacker A1 with Transport Module is an option for connecting a third party vendor finisher. For a third party vendor finisher, please contact your local FUJIFILM Business Innovation representative.

*1: 80 gsm paper.

*2: When the optional High Capacity Stacker Top Tray Extension Kit is installed, 250 sheets. For paper longer than 330 x 488 mm, the capacity is not guaranteed. 100 sheets of long paper up to 330 x 729 mm; 10 sheets of long paper up to 330 x 1200 mm can be stacked.

*3: When the optional High Capacity Stacker Top Tray Extension Kit is installed, maximum 330 to 1200 mm.

*4: Including Stacker Cart.

Interface Decurler Module D1 (Optional)

Item	Description
Power Supply	AC100-240 V +/- 10 %, 2.5 A (100 V) / 1.0 A (240 V), 50/60 Hz common
Maximum Power Consumption	250 W
Dimensions	W 340 x D 725 x H 992 mm
Weight	40 kg

Note: Interface Decurler Module D1 is necessary for connecting High Capacity Stacker A1, High Capacity Stacker A1 with Transport Module, Finisher D6, or Finisher D6 with Booklet Maker to the printer.

Crease/Two-sided Trimmer D2 (Optional)

Item	Description	
Two-sided Trim	Paper Size	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A4 Custom Size: 194 x 210 mm to 330 x 488 mm
	Paper Weight	52 to 350 gsm
	Trim dimensions	One side 6 to 25 mm
Crease	Paper Size	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min JIS B5 Custom Size: 182 x 210 mm to 330 x 488 mm
	Paper Weight^{*1}	60 to 350 gsm
	Number of lines^{*2}	1 to 5
Power Supply	AC100-240 V +/- 10 %, 4.0 A (100 V) / 2.0 A (240 V), 50/60 Hz common	
Maximum Power Consumption	480 W	
Dimensions	W 605 x D 725 x H 992 mm	
Weight	128 kg	

Note: Finisher D6 or Finisher D6 with Booklet Maker is required.

*1: When using the booklet finishing. 157 gsm or more is supported for single sheet.

*2: The continuous print speed will decrease significantly as the number of lines increases.

Square Back Fold Trimmer D1 (Optional)

Item	Description	
Paper Size	Same as the paper size of the Finisher D6 Booklet Finishing.	
Paper Weight	Same as the paper weight of the Finisher D6 Booklet Finishing.	
Booklet Tray Capacity^{*1}	20 sets ^{*2}	
Face Trim	Capacity^{*3}	Saddle Staple: 30 sheets, Single Fold: 5 sheets
	Trim dimensions	2 to 20 mm
Square Back Capacity^{*3 *4}	30 sheets	
Power Supply	AC100-240 V +/- 10 %, 1.0 A (100 V) / 0.6 A (240 V), 50/60 Hz common	
Maximum Power Consumption	100 W	
Dimensions	W 1066 x D 725 x H 552 mm	
Weight	100 kg	

Note: Finisher D6 with Booklet Maker is required.

*1: Paper may not be accepted depending on paper type and other usage conditions.

*2: 16 sets when 17-20 sheets/set, 12 sets when 21-25 sheets/set, 10 sets when 26-30 sheets/set.

*3: The capacity can decrease depending on type and weight of paper being used and other conditions.

*4: Square back finishing is not supported for single-folding and saddle stapling of less than 5 sheets.

Insertor D1 (Optional)

Item	Description
Paper Size	Standard Size: Max SRA3 (320 x 450 mm), 12.6 x 19.2" (320 x 488 mm), Min A5 Custom Size: 182 x 148 mm to 330 x 488 mm
Paper Weight	52 to 350 gsm
Paper Capacity ^{*1}	250 sheets
Power Supply	Supplied from Interface Decurler Module D1
Dimensions ^{*2}	W 700 x D 725 x H 1235 mm
Weight	45 kg

Note: High Capacity Stacker A1, High Capacity Stacker A1 with Transport Module, Finisher D6, or Finisher D6 with Booklet Maker is required.

*1: 80 gsm paper.

*2: The width of the paper transfer area when connected to the device is 165 mm.

Static Eliminator D1 (Optional)

Item	Description
Power Supply	AC100-127 V +/- 10 %, 0.6 A, AC200-240 V +/- 10 %, 0.3 A, 50/60 Hz common
Maximum Power Consumption	72 W
Dimensions	W 232 x D 725 x H 992 mm
Weight	40 kg

Note: High Capacity Stacker A1, High Capacity Stacker A1 with Transport Module, Finisher D6 or Finisher D6 with Booklet Maker is required.

Smart Monitoring Gate D1 (Optional)

Item	Description
Power Supply	AC100-120 V +/- 10 %, 2.4 A, AC200-240 V +/- 10 %, 1.2 A, 50/60 Hz common
Maximum Power Consumption	240 W
Dimensions	W 605 x D 725 x H 992 mm
Weight	92 kg

Note: High Capacity Stacker A1, High Capacity Stacker A1 with Transport Module, Finisher D6 or Finisher D6 with Booklet Maker is required.

Purchase precautions

Notes

1. If the storage media (such as hard disk drives) of the base unit fail, loss of received data, accumulated data, registered setting data, etc. may occur. In no event shall the Company be liable for any damages whatsoever arising from loss of data.
2. Functional spare parts will be available for at least 7 years after the product is no longer manufactured.

fujifilm.com/fbvn

FUJIFILM

FUJIFILM Business Innovation Vietnam Co., Ltd

Head Office

Ground floor, 2nd Floor and 19th Floor, The Hallmark Building, 15 Tran Bach Dang, Thu Thiem Ward,
Thu Duc City, Hochiminh City
Tel: (84-28) 38 290 038 Fax: (84-28) 38 290 032

Ha Noi Branch

14th Floor, VCCI Tower 9 Dao Duy Anh, Dong Da Dist., Ha Noi
Tel: (84-24) 38 241 063 Fax: (84-24) 38 241 113

Hai Phong Branch

5th Floor, TD Office Building 20A Le Hong Phong, Ngo Quyen Dist., Hai Phong
Tel: (84-225) 3859 236 Fax: (84-225) 3859 239

Da Nang Branch

3rd Floor, Danabook Building 76-78 Bach Dang, Hai Chau Dist., Danang
Tel: (84-236) 3892 896 Fax: (84-236) 3892 895

The available model varies depending on the country/region. Please ask the sales representatives for details.

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.

Reproduction Prohibitions Please note that reproduction of the following is prohibited by law : •Domestic and foreign currencies, government-issued securities, and national bonds and local bond certificates. •Unused postage stamps, post cards, etc. •Certificate stamps stipulated by law. •Reproducing works forming the subject matter of copyright (literary works, musical works, paintings, engravings, maps, cinematographic works, drawings, photographic works, etc.) is not permitted unless the reproduction is for the purpose of personal use, family use or other similar uses within a limited circle.

Trademarks •FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •Revoria, Revoria logo, Revoria Press and Revoria Flow are registered trademark or trademark of FUJIFILM Business Innovation Corp. •Adobe, Adobe logo, PostScript and PostScript logo, Adobe PDF, Adobe PDF Print Engine are either registered trademarks or trademarks of Adobe in the United States and/or other countries. •All product names and

For Your Safety

Before using the product, read the Instruction Manual carefully for proper use. Use the product with the power source and voltage specified. Be sure to establish ground connection. Otherwise, electronic shock may result in the case of a failure or short circuit.